


## Electrode E14 with EG, EL and EA-EV Pins



Electrode E14-V with BNC cable to connect Ligno-VersaTec and Lignometer K

Electrode E14-m with mini-BNC cable to connect mini-Ligno MD/C, S/DC and DX/C

The black knob at the end of the electrode can be removed and a broom-stick type handle can be attached to extend reach of electrode. No more crouching down to reach the carpet or using a ladder to reach the ceiling.

Upon request the EL pins can be shortened to any length between 7" and 1".

We include 2 black plastic stoppers, which can be used to limit the measuring depth, when measuring hard materials. Otherwise, it could be hard to remove the EG pins.



Lignomat USA Ltd, 800-227-2105,  
[www.lignomat.com](http://www.lignomat.com), [sales@lignomat.com](mailto:sales@lignomat.com)  
 14345 NE Morris Ct, Portland OR 97230 USA